

[Read More](#)

SKU:

Price:

Stock: instock

Categories: [Uncategorized](#)



Product Description

It is highly used in chemical industries, pharmaceutical industries and also higher learning institution

Features

- Digital LCD display of both rotation speed and heating temperature allows for optimal control of all distillation processes
- Automatic motor lift releases the evaporating flask to a safe position in case of power failure
- 5L heating bath with wide temperature range from room temperature to 180°C
- Water/oil heating mode can be changed only through a switch
- Overheating protection temperature at 220°C
- Boil-dry protection, automatically power off if heating without water/oil in the heating bath
- Speed range from 20 to 280rpm, and interval operation in clockwise and anticlockwise directions for drying process
- Condenser (cooling surface 1700cm²) with excellent cooling effect
- Ejection mechanism ensures easy removal of evaporating flask
- Double spring sealing ring made of PTFE provides an excellent sealing performance
- Optional glassware with explosion proof film available

Specification

- Evaporating Flask Volume : 50-5000mL (Optional Thickened glass axis compatible with 5L evaporating flask)
- Motor Type : Brushless DC motor
- Speed Range : 20-



AGN ENTERPRISES

MANUFACTURER & SUPPLIER
ALL KINDS OF LABORATORY EQUIPMENTS



465x457x583mm Weight : 15kg Permissible Ambient Temperature : 5-40°C Permissible
Relative Humidity : 80%RH Protection Class : IP20 USB Interface : Yes Voltage/Frequency : 200-
240V, 50/60Hz Power : 1500W **Optional Add-ons (Seals and other Accessories) :** vacuum
seal PTFE+Viton Evaporation bottle spring Evaporation flask clip(red) NS29/42 Evaporation flask
clip(green) NS24/40 Rotary Evaporator transparent safety shield Flask holder(50mL-1000mL)
Flask holder(1L-20L)
